











ADI FAD (Golden Delta), Barcelona 1961

In order to mark the fiftieth anniversary of this exceptional design, in 2011 Santa & Cole presented the "latest, definitive edition" (in the words of its creator) of the TMC lamp. The present version revives a number of the details that have been brushed aside throughout its heterogeneous productive life, such as the thickness and quality of the methacrylate material used in the shade or its strictly circular shape. However, it also incorporates new improvements to the up-down shade system that is no longer comprised of a row of openings at the back to insert the clamp; rather, the upper shaft is a smooth, continuous piece where the height of the shade can be adjusted using a well-positioned magnet. An undeniably unsurpassable masterpiece.

General description:

Two-part metal structure: upper half chrome-plated and lower half black.

Height-adjustable white methacrylate lampshade.

The light is switched on/off by pulling lightly on the cable (UL: On/off lamp holder switch).

Electric cable length: 4 m / 157.5"

Approximate weight (unpacked):

5kg / 11lb

Technical information:

Recommended light sources:

LED bulb: 10 W

Other light sources: Max. 100 W E27 - E26 (Max. hgt. 125 mm / 4.9")

Light source not included.

Compatible with bulbs of the Energy efficiency class (E.E.C): A++... E.

Suitable only for indoor use.

Always use the light source recommended or equivalent.

Input voltaje: 100, 120, 230 Vac.

(50 Hz / 60 Hz). According to destination

TMC

Miguel Milá. 1961 Floor Lamps



Regulations:

CF

UNE-EN 60598 UNE-EN 55015 UNE-EN 60529

Dry location only UL-153 E-352592

Maintenance:


Clean with a smooth cloth. Do not use ammonia, solvents or abrasive cleaning products.

Others:

The lamp is delivered in one package.

The assembly instructions are delivered with the product.

Model:



TMC Contract Version

Miguel Milá. 1961 Floor Lamps












Switch:

The on/off system that operates by pulling on the electric cord has been replaced by a switch on the lamp holder (or on the cord).



Height adjustment:

The height is limited to 3 positions and can be set using a thread. This attachment system prevents wear resulting from extensive use and ensures that the user cannot alter the height.

